

# Medi-Pulse Pro<sup>TM</sup>

SHR IPL SYSTEM

FASTER, SAFER & PAIN-FREE  
IPL HAIR REMOVAL & SKIN  
REJUVENATION

*Flash with confidence*

**soma**<sup>TM</sup>  
Lasers Australia





# Medi-Pulse Pro™

SHR IPL SYSTEM

We bring you the latest and best technology on the market.

An SHR IPL with pure sapphire hand pieces built in filters for more stable power output and precise treatment.

We truly are “*Best In Class*”



The gift of  
beautiful  
skin

- Super fast hair removal
- Pigmentation
- Sun damage
- Rosacea
- Acne
- RF skin tightening

# Medi Pulse Pro

## RADIO FREQUENCY

### How it works

Our Radio Frequency Skin Tightening uses the perfect power output Radio Frequency energy, it is emitted from the Medi Pulse PRO XL device in the correct amount and it safely heats up the superficial layers of your skin.

By heating your skin, the treatment causes some of your old collagen and elastin fibres to be broken down, stimulating your body to produce new, stronger collagen fibres. The Skin Tightening treatment helps your body to replenish fresh new collagen. This helps to firm and tighten your skin, giving you a younger, fresher looking appearance.

### The benefits

Following a course of Radio Frequency Skin Tightening treatments, you'll notice tighter, firmer skin and a fresher appearance. Our Radio Frequency is suitable for use on a wide range of areas, including a Skin Tightening Facial for your face, neck, décolletage and eyes.

This skin tightening treatment can also be used on areas of your body including your stomach, thighs and even your hands.

Radio Frequency Skin Tightening facial and body treatments are painless, effective and safe. RF is a popular choice for people looking for a pain-free experience with great results.

### Which areas can be treated?

*On the face it can treat:*

- Sagging face skin and neck skin
- Loose jowls
- Lack of definition in the jaw line
- Wrinkles and fine lines
- Lack of definition in the lips

*On the body it can treat:*

- Sagging or bulging skin
- Loose skin
- The appearance of cellulite



### Recommended treatment course

We usually recommend a course of 6-8 Radio Frequency Skin Tightening treatments, spaced 1-2 weeks apart for the best results. Results start to show once your body has had time to regenerate some of your collagen, usually towards the end of your course and will continue to improve for around 8 weeks when the full results can be seen.

## Handpieces

Our hand pieces have pure sapphire tips NOT glass. Pure sapphire has a much higher light transmission than glass. For example if you set the energy to 10J/cm you will get 10J/cm, whereas with glass you are more likely to actually get 5J/cm with the same settings. Our Filters also are Pure Sapphire.

## Filters

You want to be able to get the most from your IPL SHR device. We give you a choice between different wavelengths to target different skin conditions, as well as hair removal. For example a 430nm filter is great for treating acne, whereas a 690nm filter is perfect for permanent hair reduction.

We also have the 690nm built into our actual HR hand piece where there is no need to apply a filter.

Filters allow you greater flexibility with treating different skin types, so for the HR (Hair Removal SHR) hand piece we also have a 750 filter for quite darker skin tones.

Having this built-in filter in your hand piece guarantees no energy leakage.

For the SR (Skin Rejuvenation) hand piece however we do need different filters to tackle different diseases which use different wavelengths to break down melanin in the skin, eliminating pigmentation, discolouration, smoothing out skin tone, redness, broken capillaries, also calming and repairing acneic skin.

\* Please make sure when choosing your device to check your warranty! Not only on your device but also your hand pieces. Make sure the company you choose offers at least 300,000 shot warranty... we do..

Our hand pieces can reach up to 1 million shots.





*“Quality in a product is not only what you put into it. It is what the customer gets out of it.”*

*~ Soma Lasers Australia*

*Unmatched, incomparable device made with the therapist in mind*

Soma devices are made with the highest quality engineering working together with Germany, Korea, Japan the USA and proudly designed in Australia for fantastic durability.

The new technology in this device is seriously unsurpassed. Filter changing is a thing of the past! Everything is programmed for you. In-built filters means more stable power output. Your treatments will blow you away.

Strong, smart, beautiful, a device you can count on for years to come.

*Warranty*

We back up our promise at Soma Lasers Australia, with a 3 year warranty on all our new medical aesthetic devices.

*Marketing*

This is a BIG one! What's the point of investing in new technology for your salon or clinic, if you're not attracting any clients? Some of the biggest concerns we hear is 1) How can I feel certain that I will make my money back and 2) I don't know what to post on social media. This is why Soma Lasers Australia INT sets you up with a great kick-start on your marketing! \$2000 Free Marketing Campaign! We guarantee you customers!

YES! We offer you a complete package because we know how daunting it is to set up a successful business!!!

| Specifications       |  |
|----------------------|--|
| Spectrum             | HR 640, 690, 755-1200nm<br>SR 430, 480, 530, 590, 640, 690, 755-1200nm |
| IPL SHR Energy       | 1-50J/cm <sup>2</sup>  |
| Pulse Width          | 2-10ms   |
| Pulse Delay          | 5-60ms   |
| SHR Frequency        | 1-15Hz   |
| Spot Size            | HR + SHR 16x50mm <sup>2</sup><br>SR + SSR 10x40mm <sup>2</sup>         |
| RF Energy            | 10M  |
| RF Power             | 200W   |
| Treatment Tips       | 20mm, 30mm and 36mm  |
| Cooling              | semiconductor cooling + water cooling + air cooling                    |
| Cooling Temperature  | -8 to 0 degrees  |
| Continuous Work Time | 13 hours   |
| Power                | 2000W  |
| Voltage              | AC100-120V or 220-240V   |
| Dimensions           | 470mm x 590mm x 455mm  |
| Weight               | 25kg   |

*Equip your salon or clinic with*



M: +61 403 744 648  
E: support@somalasersaus.com.au  
W: www.somalasersaus.com.au

Our demonstration suite is situated at:  
3/10 Atherton Road, Oakleigh Vic 3166